

## Settings Lock Feature

CR2 firmware versions 2232 and above, includes the following new feature:

The CR2 now has a "Settings Lock" setting where you may lock the reader settings to prevent unintentional changes.

To enable "Settings Lock" feature scan the Lock Reader Settings programming code (M429\_01) below:

### Lock Reader Settings



M429\_01

To disable "Settings Lock" feature scan the "Settings Unlock" programming code (M428\_01)

### Unlock Reader Settings



M428\_01

These new codes are also in the CR2 Users Manual and in the CR2 Users Manual Appendix C. <http://www.codecorp.com/support/usermanuals.htm>

### \*\*\*\*\*PLEASE NOTE\*\*\*\*\*

Prefix and Suffix programming codes, memory transfer and delete commands, "Clear All CodeXML Rules" and "Suffix Erase/None" commands are not locked by this feature.

If you have any additional questions regarding this feature please contact Code Corporation Technical Support at [support@codecorp.com](mailto:support@codecorp.com) or call (801) 495-2200 x600